

NANOPB


NANO Proximity Reader - Wiegand

The NANO from CDVI is a mini and compact proximity card reader.

This stylish reader is available in black. As with the other readers from the range (STAR, SOLAR, SOLARK and MOONAR), the NANO gives an anytime status of the door through multi-coloured LED's.


This access control reader has a high performance read range and is easy to mount.

We, CDVI, declare that the NANO radio equipment complies with directive 2014/53/UE. The full text of the EU declaration is available at www.cdvi.com




NANOPB

- Wiegand 26, 30 or 44-bit
- Audible and visual feedback
- Reads CDVI 125 kHz cards and tags
- Up to 4 in. (10 cm) read range
- Power requirements: 12V DC
- Current consumption: 150 mA
- Multicoloured LED:
 - Blue: Standby
 - Green: Access Granted
 - Red : Access Denied



RFID Frequency band: 125 kHz. Maximum transmitted power below the allowed limit: <60dBμA/m

MOUNTING





					
1	2	2	1	1	1

Important

Keep at least 60 cm (24") between two readers.

WIRING DIAGRAM



Cable	
Red	Input voltage 12V dc
Black	0V
Blue	Clock
Green	Data 0
White	Data 1
Brown	Buzzer
Yellow	Green LED
Orange	Red LED

LED & AUDIBLE TONE

When powered

- Green LED illuminates for 1 second
- Red LED illuminates for 1 second
- Buzzer sounds for 1 second

Operating mode

- Buzzer activated with 0V input
- LEDs activated with 0V input


Green LED	Red LED	Status
OFF	OFF	OFF
OFF	ON	red
ON	OFF	green
ON	ON	blue

Card Swiped

- *Badge recognized*: the orange LED illuminates and the buzzer activates for 150 milliseconds.
- *Badge not recognized*: no change.

Wiegand output formats

DIP1	DIP2	BITS
OFF	OFF	26
ON	OFF	30
OFF	ON	44



CDVI SAS
31 Général Leclerc Ave
93500 PANTIN
01 48 91 01 02



NANOPB

Lecteur NANO de proximité - Wiegand


Le NANO de CDVI est un lecteur de cartes de proximité compact.

Ce lecteur élégant est disponible en noir. Comme avec les autres lecteurs de la gamme (STAR, SOLAR, SLOARK et MOONAR), le NANO affiche le statut de la porte à tout moment grâce à des LED multicolores.


Ce lecteur de contrôle d'accès a une plage de lecture haute performance et est facile à installer.

Nous, CDVI, déclarons que l'équipement radioélectrique NANO est conforme aux exigences de la directive européenne 2014/53/UE. La déclaration UE de conformité est accessible sur www.cdvi.com.

- Wiegand 26, 30 ou 44 bits
- Signalisation lumineuse et sonore
- Cartes et badges CDVI 125 kHz
- Jusqu'à 10 cm de portée
- Alimentation : 12V DC
- Consommation : 150 mA
- Voyant LED (3 couleurs) :
 - Bleu : veille
 - Vert : accès autorisé
 - Rouge : accès refusé










NANOPB



Bande de fréquence RFID: 125 kHz
Puissance maximale transmise en dessous de la limite maximale autorisée <60dBμA/m

MONTAGE




					
1	2	2	1	1	1

Important

Laissez un espace d'au moins 60 cm (24") entre deux lecteurs.

RACCORDEMENTS



Raccordement	
Rouge	Alimentation 12 V DC
Noir	0 V
Bleu	Clock
Vert	Data 0
Blanc	Data 1
Marron	Buzzer
Jaune	Voyant vert
Orange	Voyant rouge

FONCTIONNEMENT

Mise sous tension

- Voyant vert pendant 1 seconde
- Voyant rouge pendant 1 seconde
- Voyant bleu pendant 1 seconde avec bip

Fonctionnement

- Activation Buzzer par niveau 0 V
- Activation voyants par niveau 0 V


Voyant vert	Voyant rouge	Etat
OFF	OFF	éteint
OFF	ON	rouge
ON	OFF	vert
ON	ON	bleu

Présentation badge

- Badge lu : voyant orange et bip pendant 0,15 seconde puis retour suivant état activation en cours.
- Badge non lu : pas d'effet.

Formats de sortie Wiegand

DIP1	DIP2	BITS
OFF	OFF	26
ON	OFF	30
OFF	ON	44



CDVI SAS
31 avenue du Général Leclerc
93500 PANTIN
01 48 91 01 02

